
Enjoy your Hoopo® Hydr

Is there anything else we can do for you? Go to hoopo.eu/service

Product & components

- USB charging port (type-C)
- Indicator Light
- 9 Power Button
- Water Plate
- Silver Nanoparticles Filter
- 6 Water outlet
- Filter Tray
- Water tank
- USB charging cable


Exploded view



Hoopo® Hydr

Patented design

How to Hydr









Hoopo-Hydr-Manual-400x200mm-20250225.indd 1

How to use

Power on: Press and hold the button for 2 seconds to power on, accompanied by a short "beep" sound prompt.

Power off: In the power-on state, press and hold the button for 2 seconds to power off, accompanied by a long "beep" sound prompt.

Operation Description:

- After the device is turned on, it will automatically discharge water for 20 seconds every 30 minutes.
- 2 After the device is turned on, it will automatically turn on the UV lamp for disinfection for 10 minutes every 24 hours.

Indicator light: power-on condition.

- 1. White light is always on: normal work.
- Flashing blue light: low water level reminder, need to add water.
- Steady blue light: water change reminder, water needs to be changed. (seven days since the last operation)
- Blinking red light: low battery reminder, needs to be charged.
- 5. Steady red light: charging. When fully charged the light switches of.

Operation: power-on condition.

- Press the button to discharge water for 20 seconds. During the water discharge process, press the button to stop the water discharge.
- 2 Double press the button to enter the 10-minute disinfection state by default configuration. In the disinfection state, doublepress the button again to cancel the operation of the disinfection lamp beads.

Reminder: Do not look directly at the UV Germicidal lamp when it is working.

Maintenance

- The water tank and separate parts should be hand-washed every week using a biological, non-toxic soap.
- Descale the Hydr fountain every 2 weeks using biological household vinegar. After descaling, be sure to flush the product thoroughly with plenty of water.
- The pipe can be cleaned with a soft brush.

Filters replacement

4 channel filters for cleaner water, replace every 5-10 days for the best result.

Specifications

Product name	Hoopo® Agua (Wireless Water Dispenser)
Product material	ABS+PP+Silica Gel
Product weight	≈600g
Dimensions	L240*W130*H135mm
Water tank capacity	1800ml
Power type	Button Press
Water level sensor	≤ 500ml
Water outlet timing	20s/30mins
Battery	Lithium Battery 18650*2
Battery capacity	4400mAh
Battery life	Approx 30 Days
Charging time	3-4h
Sterilization lamp time	10 mins
Water dispensing time	20s per session every 30 mins

Attention!

For you and your pet's safety, please read the following instruction carefully:

- · Do not disassemble or repair this device personally.
- Do not knock or drop the device, repeated knocks may cause internal components damage.
- · Please use this unit in an indoor environment.
- If cleaning the whole machine, please cut off the power and turn off the product first.
- When charging the product, do not let pets chew on the wires to avoid leakage.
- If a child is operating the device, be sure to do so under the supervision of an adult.
- When using the product, keep it horizontal and do not overturn the device.
- For optimum use, the amount of water should be kept at the recommended level.
- For safety reasons, we recommend that you do not use the product while it is charging.

A Warning

- When using the device, do not block the water outlet.
- The product must not be thrown into water or fire, if abnormal conditions occur. Please stop using it immediately.
- It is forbidden to disassemble and clean the product during operation.

Warranty

- Your appliance warranty is valid for 2 years from the date of purchase.
- The right of interpretation of this warranty card belongs to the company.
- For artificial damage, the customer is responsible for the repair cost and delivery costs.
- This Limited Warranty applies only to flaws caused by production, technical and quality reasons only.

Hoopo-Hvdr-Manual-400x200mm-20250225,indd 2